

# Transfer 26 Acrylic Outward Swing Door Walk-In Bathtub Specifications

**Actual Size:** 26" x 52" x 40" • (66.04cm x 132.08cm x 101.6cm)

**Shipping Size:** 29" x 60" x 50" • (73.66cm x 152.4cm x 127cm)

**Net Weight:** 205lbs • (92.98kg)

Shipping Weight: 300lbs · (136.07kg)

**Seat Width:** 19" • (48.26cm)

**Unoccupied Water Capacity:** 75gal · (283.9L)

**Occupied Water Capacity:** 35-55gal • (132.48 - 308.19L)

#### **Included Features (Soaking)**

- 1. Acrylic shell gloss white finish fiberglass gelcoat reinforced
- 2. Stainless steel frame with adjustable leveling legs
- 3. Plastic composite and tempered glass outward swing door with 2 latch gear & shaft mechanism
- 4. Removable front apron with two access panels
- 5. One reversible end panel & extension panel 8"
- 6. Stainless steel chrome finish deck and wall-mounted grab bar
- 7. Two 2" 4-port PVC drains with 2 end caps included, 2 overflows, 2 stainless steel operated openers with extended handles in chrome finish

#### **Jetting & Therapy Options**

- 1. Air + Hydro (LED Chromatherapy Light Included)
- 2. Hydro + Hydro Independent Foot Massage (LED Chromatherapy Light Included) \* (2)
- 3. Hydro Massage + Microbubble (LED Chromatherapy Light Included)
- 4. Hydro Massage (LED Chromatherapy Light Not Included)
- 5. Soaking

### **Jetting & Therapy Systems**

#### **Hydro Massage**

- ·Hydro Massage Pump 7A
- ·Intensity Dial Air Control
- ·Ozone Sterilization 0.04A
- ·13 jets (7 Seat Jets 6 Foot Jets)
- •On/Off Push Control
- In-line Water Heater 6A 650W

#### **Hydro + Hydro Foot Massage \*(2)**

- •2 Hydro Massage Pumps 5A + 7A
- •2 Intensity Dial Air Controls
- •Ozone Sterilization 0.04A
- •13 jets (7 Seat Jets 6 Foot Jets)
- ·On/Off Push Control
- •In-Line Water Heater 6A 650W

#### Air Massage

- ·Air Massage Pump 4.5A 500W
- ·3 Speed Pump
- •Auto-purge (Activates 20 minutes after pump shutdown)
- •17 jets (11 Seat Jets 6 Foot Jets)
- On/Off push control

#### **Optional Features**

1.Heated Seat and Backrest2.Digital Controller

### Microbubble Therapy

- •1 HP Pump 7.3A
- Pressure Vessel
- ·On/Off push control
- Agitator Valve

#### **Electrical Requirements**

Dedicated GFCI protected electrical line(s)required 115/120V 60Hz

**Note:** LED Chromatherapy light 0.5A with On/Off push control is included with the following dual packages: Hydro + Air, Hydro + Micro, Hydro + Hydro

**Disclaimer\***: AMP value for each pump may change based on availability. Please verify before purchase. (800.480.6850)

#### 2 Piece Faucet

• Up to 16GPM @ 60PSI (at ideal

in-home plumbing conditions)

- Two 5' Water Supply Lines 3/4"
- Pull out Hand Shower in

Chrome Finish with a 5'

Retractable Stainless Steel

Braided Hose

#### Warranty

- Lifetime limited\* warranty on shell, frame, door, and parts to original purchaser/Address
- Labor or installation is not covered please refer to the Ella warranty certificate
- Non Ella brand faucets covered under manufacturers original warranty


ellasbubbles.com Page 1 of 7 6/7/23



ellasbubbles.com

### Transfer26 Acrylic Wheelchair Accessible Outward Swing Door Walk-In Bathtub Specifications


6/7/23



Page 2 of 7




### Transfer26 Acrylic Wheelchair Accessible Outward Swing Door Walk-In Bathtub Specifications





### Ella 2" T-type Dual Port Floor Drain

### Dual Drain Technology - Two 2 Inch Independent Floor Drains





### Supply Lines, Electrical Connection, & Drain Options

Two 3/4" connector water supply lines included with Ella Fast Fill Faucets

Connect to Shut Off Valves (not included)








All electrical fixtures connect to a dedicated GFCI protected outlet or GFCI protected Circuit Breaker.









T-Type four (4) 2" drain ports allow for the drain pipe to be installed in either Side Of The Drain unused Port. direction.



Drain Caps Installed On Either









## Ella 2 Piece Single Lever Fast-Fill Faucet

**Description**Solid brass spout in a chrome finish with a 5-setting pull out hand shower mixer with back-flow prevention valve this includes a 5' braided hose. Two 3/4" 5' braided stainless-steel supply lines are included along with Cold/Hot levers with a diverter for the hand mixer

#### Flow

- · Hand shower is limited to 1.9 GPM (7.5L/min)
- Faucet fill rate designed for 16 GPM (68.1L/min)

#### Cartridge


- · 40mm high flow cartridge design
- Nonmetallic/nonferrous and stainless-steel material

#### **Standards**

- Third party certified to meet: CSA B125.1, ASMEA112.18.1, ICC117.1 and all applicable requirements referenced therein
- Certified to ANSI/NSF 61/9
- · ADA for lever/handle
- IAPMO R&T UPC certified



NOTE: This faucet is designed to be installed through 2-1/2" diameter hole for faucet, 1/3" diameter hole for mounting rods, and a 7/8" diagonal hole for the hand shower.






### Replacing A Valve Cartridge

Step-by-step Instructions to replace a valve cartridge for Ella 2-piece faucets.

Step.1 Remove the Hot/Cold screw hole cover.



Step.2 Use an Allen wrench to remove the handle Screw.



Step.3 Take out the handle and remove the brass escutcheon



Step.4 Use a wrench to unscrew the pressure cap.



Step.5 Remove the cartridge and replace it with new piece.



